

TECHNICAL DATA SHEET

WHITECH3040M - 750 ‰

Master alloy for the production of white nickel free 750 ‰ gold jewellery obtained by mechanical working. This product, thanks to its complex composition made of numerous different special elements, ensures an extreme quality, an enhanced fluidity and a long lasting of this features also after many reuses of scraps, making it the most advanced nickel free master alloy for white gold.

TAB.1 - Mechanical data

Hardness as cast	200	HV
Hardness hardened	n.d.	
Tensile strength	n.d.	
Yield strength	n.d.	
Elongation	n.d.	

TAB.2 - Physical data

Color	Premium white		
Colour Coordinates	L*:	80.12	
	a*:	2.06	
	b*:	6.41	
Density	15.74	g/cm ³	
Melting Range	Solidus:	950	°C
	Liquidus:	1050	°C

TAB.3 - Heat treatments

Solution annealing	630 30	°C min
Recrystallization Annealing	630 30	°C min
Hardening	n.d.	

TAB.4 - Mechanical working parameters

Premelting temperature	see paragraph below		
Casting Temperature	Min:	1100	°C
	Max:	1200	°C
First thickness reduction	Lamination:	50	%
	Drawing:	25	%
Following thickness reductions	Lamination:	75	%
	Drawing:	50	%
Pickling after annealing	see paragraph below		

PREMELTING (MANDATORY)

A premelting of the master alloy and fine gold must be done to homogenize the alloy in the best way. For a proper premelting, first put the fine gold in the crucible and then switch on the power until 1100°C (make sure that the metal becomes liquid). After this, put the master alloy inside the liquid gold and, with a stirrer, push down the master alloy inside the gold, then decrease the temperature to 950-1000°C and pour into an ingot or do a granulation.

PICKLING

For a proper pickling, use a concentrated solution of sulfuric acid at 60 - 65°C for 20 mins or a 50 % solution of hydrochloric acid at 60 - 65° C for 10 min.